









REV.	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E0230307	PEI 07/11/02	JMR
2	REVISED PER E080070	SA 01/11/08	REJH
3	REVISED PER E091753	JS 09/29/09	REJH
4	REVISED PER E092276	JS 12/30/09	REJH
5	REVISED PER E120065	VSS 01/20/12	KUK



DASH NO.	SOCKET BODY LENGTH	DIM "A"	DIM "B"	INPUT	OUTPUT	KIT#
-01	.100/2.54	.280/7.11	.280/7.11	18378	18388	18364
-02	.135/3.43	.315/8.00	.315/8.00	18379	18389	18365
-03	.160/4.06	.340/8.64	.340/8.64	21539	21543	21510

- NOTE:
- MATERIALS: INMATES: PPS RYTON 7
SOCKETS: BE-CU #25, Au PLATED.
 - FULLY SEAT SOCKET INTO INMATE HEADER.
 - ROHS COMPLIANT PER CST-0001 LATEST REVISION.



DRAWN BY Lap Nguyen	DATE 6/99	VICOR	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE : INCH / (MM)		DWG, VI-900 INMATE/SOCKET, BOB	
TOLERANCES ARE: DECIMALS XXX (X.X) = ±0.01 (0.25) X.XXX (X.XX) = ±0.005 (0.127)		SIZE D 67131	REV 5
THIRD ANGLE PROJECTION DO NOT SCALE DRAWING		SCALE 4:1	SHEET 1 OF 1