









| REV. | DESCRIPTION         | DATE         | APPROVED |
|------|---------------------|--------------|----------|
| 2    | REVISED PER E080070 | SA 01/15/08  | REJH     |
| 3    | REVISED PER E091753 | JS 09/29/09  | REJH     |
| 4    | REVISED PER E092276 | JS 12/30/09  | REJH     |
| 5    | REVISED PER E120065 | VSS 01/20/12 | KUK      |



| DASH NO. | SOCKET BODY LENGTH INCH/MM | DIM "A" INCH/MM | DIM "B" INCH/MM | INPUT | OUTPUT | KIT # |
|----------|----------------------------|-----------------|-----------------|-------|--------|-------|
| -01      | .100/2.54                  | .243/6.17       | .243/6.17       | 18374 | 18384  | 18366 |
| -02      | .135/3.43                  | .278/7.06       | .278/7.06       | 18375 | 18385  | 18367 |

- NOTE:
- MATERIALS: INMATES: PPS RYTON 7  
SOCKETS: BE-CU #25, Au PLATED.
  - FULLY SEAT SOCKET INTO INMATE HEADER.
  - ROHS COMPLIANT PER CST-0001 LATEST REVISION.



|                                                                                                     |              |                                |                       |          |
|-----------------------------------------------------------------------------------------------------|--------------|--------------------------------|-----------------------|----------|
| DRAWN BY<br>LAP NGUYEN                                                                              | DATE<br>6/99 | VICOR                          |                       | SWD      |
| UNLESS OTHERWISE SPECIFIED<br>DIMENSIONS ARE: INCH / (MM)                                           |              | DWG, VI-800 INMATE/SOCKET, BIB |                       |          |
| TOLERANCES ARE:<br>DECIMALS ANGLES<br>XXX (X.X) = ±0.01 (0.25) ±1°<br>X.XXX (X.XX) = ±0.005 (0.127) |              | SIZE<br>D 67131                | CAGE CODE<br>18482-XX | REV<br>5 |
| THIRD ANGLE PROJECTION<br>DO NOT SCALE DRAWING                                                      |              | SCALE 4:1<br>SHEET 1 OF 1      |                       |          |