







VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR
HEREWITH IS NOT TO BE REPRODUCED, USED OR
DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT
THE PERMISSION OF VICOR CORP.

REV.	DESCRIPTION	INTL	DATE	APVD
1	RELEASED PER E150329	GCK	03/27/15	YN
2	REVISED PER E150505	ESD	05/08/15	REJH
3	REVISED PER E150672	AWT	06/19/15	REJH
4	REVISED PER E150763	JF	07/22/2015	AWT



DIM 'L'	
SHORT	.103 [2.607]
LONG	.182 [4.613]



PRODUCT	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'	DIM 'F'
2414 (0 STAGE) 2223	1.13 [28.70]	NA	2.38 [60.42]	1.984 [50.384]	.957 [24.304]
2814 (1 STAGE) 2223	1.59 [40.34]	NA	2.84 [72.05]	2.442 [62.017]	1.415 [35.945]
2914 (0 STAGE) 3623	1.13 [28.70]	.811 [20.593]	2.93 [74.30]	2.529 [64.236]	.957 [24.304]
3414 (1 STAGE) 3623	1.59 [40.34]	.811 [20.593]	3.38 [85.93]	2.988 [75.897]	1.415 [35.945]
3714 (1 STAGE) 4623	1.61 [40.93]	1.150 [29.200]	3.75 [95.13]	3.350 [85.092]	1.439 [36.554]
4414 (1 STAGE) 6123	1.61 [40.93]	1.757 [44.625]	4.35 [110.55]	3.957 [100.517]	1.439 [36.554]
4914 (2 STAGE) 6123	2.17 [55.15]	1.757 [44.625]	4.91 [124.77]	4.517 [114.741]	1.999 [50.777]
5614 (1 STAGE) 9223	1.61 [40.93]	2.970 [75.445]	5.57 [141.37]	5.171 [131.337]	1.439 [36.554]

NOTES:

- 1- RoHS COMPLIANT PER CST-0001 LATEST REVISION.
- 2- SEE PRODUCT DATA SHEET FOR PIN DESIGNATIONS.

DRAWN BY		DATE		 VICOR		SWD	
R.E.J. Hickey		1/26/2015					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE : INCH ([MM])				PROD OUTL PCB MNT ALWAYS ON ADAPTER			
TOLERANCES ARE: DECIMALS ARE: X.XX (X.XX) ± 0.01 (0.25) ¹ / ₁₆ " X.XXX (X.XXX) ± 0.005 (0.127)							
THIRD ANGLE PROJECTION							
		SIZE		DWG NO		REV	
DO NOT SCALE DRAWING		D 67131		42015		4	
SCALE 2:1				SHEET 1 OF 1			