







VICOR CONFIDENTIAL
THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR HEREWITH IS NOT TO BE REPRODUCED, USED OR DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT THE PERMISSION OF VICOR CORP.



REV.	DESCRIPTION	DATE	APPROVED
2	REVISED PER E080070 SA	01/15/08	REJH
3	REVISED PER E091753 JS	09/29/09	REJH
4	REVISED PER E092276 JS	12/30/09	REJH
5	REVISED PER E120065 VSS	01/20/12	KUK



DASH NO.	SOCKET BODY LENGTH INCH/MM	DIM "A" INCH/MM	DIM "B" INCH/MM	INPUT	OUTPUT	KIT#
-01	.100/2.54	.243/6.17	.243/6.17	18376	18386	18370
-02	.135/3.43	.278/7.06	.278/7.06	18377	18387	18371

NOTE:

1. MATERIALS: INMATES: PPS RYTON 7
SOCKETS: BE-CU #25, Au PLATED.
2. FULLY SEAT SOCKET INTO INMATE HEADER.
3. ROHS COMPLIANT PER CST-0001 LATEST REVISION.



DRAWN BY		DATE		 VICOR		SWD
LAP NGUYEN		6/99				
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE: INCH [MM]				VI700 INMATE/SOCKET, B1B		
TOLERANCES ARE: DECIMALS ANGLES X.XX [X.X] ± 0.01 [0.25] 11° X.XXX [X.XX] ± 0.005 [0.127]						
THIRD ANGLE PROJECTION						
 DO NOT SCALE DRAWING		SIZE	CAGE CODE	DWG NO	REV	
		D	67131	18481-XX	5	
SCALE 4:1				SHEET 1 OF 1		