

F

E

D

C

B

A

F

E

D

C

B

A

8

7

6

5

4

3

2

1

VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR
HEREWITH IS NOT TO BE REPRODUCED, USED OR
DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT
THE PERMISSION OF VICOR CORP.

REVISIONS

REV

DESCRIPTION

DATE

APPROVED

SEE SHEET 1

PROFILE COMMON FOR


30140

FULL R TYP

R.015 MAX TYP

.195
(3) PL

0.005



NOTES:

1. MATERIAL ALUMINIUM: 6063-T5
2. BREAK ALL EDGES AND SHARP CORNERS.
3. RoHS COMPLIANT PER CST-0001 LATEST REVISION.
4. DIMENSIONS ARE INCHES ONLY.

DRAWN BY

DATE


P.E.IENI

05/14/2010

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE : INCH / [MM]

TOLERANCES ARE:
DECIMALS ANGLES
X.XX [X.X] = ±0.01 [0.25] ±1°
X.XXX [X.XX] = ±0.005 [0.127]

THIRD ANGLE PROJECTION



DO NOT SCALE DRAWING

 **VICOR** SWD

**HEATSINK XFLOW MINI-MOD .40
HG**

SIZE

B

CAGE CODE

67131

DWG NO

30140

REV

6

SCALE 2:1

SHEET 2 OF 2

8

7

6

5

4

3

2

1