

F

E

D

C

B

A

F

E

D

C

B

A

8

7

6

5

4

3

2



1

VICOR CONFIDENTIAL

THIS DOCUMENT AND THE DATA DISCLOSED HEREIN OR
HEREWITH IS NOT TO BE REPRODUCED, USED OR
DISCLOSED IN WHOLE OR IN PART TO ANYONE WITHOUT
THE PERMISSION OF VICOR CORP.

REVISIONS

REV	DESCRIPTION		DATE	APPROVED
1	RELEASED PER E064424	REJH	08/16/06	MB
2	REVISED PER E101309	KUK	10/22/10	AR
3	REVISED PER E190025	CL	01/17/19	DH
4	REVISED PER E190103	CL	02/20/19	DH
05	REVISED PER RW072226	CCI	07/27/26	REW



NOTES:
1. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION.

3	A/R	-	81-00004	ADHESIVE, SICOMET 7000 AND / OR LOCTITE	38240
2	2.2	IN.	56-00002	WIRE, COPPER, SOLID. #14AWG, MAGNET	
1	1	EA	36-00003	CORE, .2uH, OUTPUT	MICROMETALS-T38-26
ITEM	QTY.	U/M	PART NO.	DESCRIPTION	MAT'L. SPEC.

	DRAWN	DATE			SWD	
	P.E.IENI	08/15/05				
MATERIAL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCH [MM] TOLERANCES ARE: DECIMALS ANGLES X.XX [X.X] = ±0.01 [0.25] ±1° X.XXX [X.XX] = ±0.005 [0.127]		INDUCTOR ASSY OUTPUT, .2uH			
FINISH	THIRD ANGLE PROJECTION		SIZE	CAGE CODE	DWG NO	REV
			B	67131	30268	05
	DO NOT SCALE DRAWING		SCALE 6 : 1			SHEET 1 OF 1

