

F

E

D

C

B

A

F

E



D

C

B


A

REVISIONS				
REV	DESCRIPTION		DATE	APPROVED
1	RELEASED PER E060461	PEI	02/01/06	MB
2	REVISED PER E064534	REJH	10/17/06	MB
3	REVISED PER E070923	SRG	05/01/07	EM
4	REVISED PER E080938	SA	05/06/08	REJH
5	REVISED PER E101309	KUK	10/22/10	AR



- NOTES:
1. ASSEMBLY TO BE FREE OF NICKS.
 2. WINDINGS TO BE EVENLY SPACED.
 3. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION.
 4. GENERAL WORKMANSHIP STANDARDS FOR MAGNETIC COMPONENTS PER WS-0002.
 5. DENOTES CRITICAL CHARACTERISTIC FOR LOT INSPECTION.
 6. BOND THE MOUNT ITEM 3 IF APPLICABLE TO INDUCTOR LEADS (2 POSITIONS) USING EPOXY ITEM 7.

REF VICOR P/N 29764
REF VICOR P/N 33206



TEST	1 KHz @ 10 mV	2	PRI	20	14.7- 22.1	8 MAX
		ITEM NO.	WINDING	NO. OF TURNS	IND.(uH)	DC RES (mΩ)

MATERIAL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCH [MM] TOLERANCES ARE: DECIMALS ANGLES X.XX [X.X] = ±0.01 [0.25] ±1° X.XXX [X.XX] = ±0.005 [0.127]
FINISH	
	THIRD ANGLE PROJECTION  DO NOT SCALE DRAWING

			SWD
ASSY DWG IND TOR .98 DIA 1W			
SIZE B	CAGE CODE 67131	DWG NO 32065	REV 5
SCALE 4 : 1			SHEET 1 OF 1